



Flap disc 115 mm P 40, ceramic grain

- Extremely high material removal with little effort thanks to the self-sharpening ceramic grain.
- Excellent results for surface and edge grinding of steel and stainless steel. Ideal for extreme grinding jobs like processing high-alloy steels, titanium alloys, nickel-based alloys as well as chromium and chromium-nickel steels, brass and bronze thanks to high load capacity.
- Very high tool life; cool grinding on surfaces and edges
- Uniform grinding result, comfortable grinding with only low vibration
- Maximum working speed 80 m/s
- Tilted version: angle of attack 7-9°

Order no.	62616600
EAN code	4007430217783
Diameter x bore	115 x 22.23 mm // 4 1/2 x 7/8 "
Grit	P 40
Version	sloping
Maximum speed	13300 rpm
Sales unit / packaging unit	1 / 10