



**Flap disc 125 mm P 60, aluminium oxide, steel, non-ferrous metals, curved type**

- Suitable for rough and intermediate grinding of steel, non-ferrous metals, wood and plastics
- High lamellar lining on fibreglass pad
- Uniform grinding capacity
- Cool grinding
- Low noise level
- Uniform grinding result, comfortable grinding with only low vibration
- Maximum working speed 80 m/s
- Tilted version: angle of attack 7-9°

<b>Order no.</b>	<b>624396000</b>
<b>EAN code</b>	<b>4007430444035</b>
Diameter x bore	125 x 22.23 mm
Grit	P 60
Version	sloping
Maximum speed	12200 rpm
Sales unit / packaging unit	1 / 10