



10 Sanding belts 40 x 760 mm, P120, zirconia alumina, for pipe belt sanders

- For all metal uses, particularly suited for processing stainless steels/Inox. High performance sanding belt, dense with cotton base.
- High material removal with good service life. Even grinding result.
- For rough-polishing and deburring of steel and stainless steel
- Recommended circumferential speed: 25-35 m/s

Order no.	626307000
EAN code	4007430194787
Dimensions	40 x 760 mm // 1 9/16 x 30 "
Grit	P 120
Sales unit	10