



Fibre disc 115 mm P 24, ceramic grain

- Self-sharpening ceramic grain for extremely high material removal with little effort
- Excellent results for surface grinding of steel and stainless steel. Ideal for extreme grinding jobs such as processing high-alloy steels, titanium alloys, nickel-based alloys as well as chromium and chromium-nickel steels, brass and bronze, thanks to high load capacity.
- Very high tool life; cool grinding
- Ceramic filter discs achieve their best performance on powerful angle grinders with increased down pressure.
- Fibre discs for clamping on backing pad! The backing pads with cooling fins are recommended for clamping the ceramic fibre sanding discs (e.g. Ø 125 mm, 623291000)
- Maximum working speed 80 m/s

Order no.	62615000
EAN code	4007430217882

Diameter x bore	115 x 22.23 mm
Grit	P 24
Maximum speed	13300 rpm
Sales unit / packaging unit	1 / 25