



Flap disc 76 mm P 60, zirconia alumina, steel, stainless steel, straight version

- Suitable for rough and intermediate grinding in all fields of metalworking including stainless steel, steel, cast iron, and sheet steel
- High lamellar lining on fibreglass pad
- Uniform grinding capacity
- Cool grinding
- Low noise level
- Uniform grinding result, comfortable grinding with only low vibration
- Most suitable for processing stainless steels
- Maximum working speed 80 m/s; flap disc in slanted version; angle of attack 7-9°

Order no.	626875000
EAN code	4061792174252
Diameter x bore	76 x 10 mm // 3 x 0.4 "
Grit	P 60
Version	straight
Maximum speed	20100 rpm
Sales unit / packaging unit	1 / 1