



10 Sanding belts 40 x 760 mm, P80, ceramic grain, for pipe belt sanders

- For all metal uses, particularly suited for processing stainless steels/Inox. Flexible high performance sanding belt, semi-open coarseness with cotton base
- Extremely high material removal with extremely high tool life thanks to the self-sharpening ceramic grain. Even grinding and best results.
- For pre-polishing and fine polishing, for example, of contours, profiles, etc.
- Recommended circumferential speed: 25-35 m/s for stainless steel
- Recommended circumferential speed: 20-30 m/s for NF metals
- Recommended circumferential speed: 5-10 m/s for high temperature Ni-/Co steels

| | |
|------------------|----------------------|
| Order no. | 626309000 |
| EAN code | 4007430194800 |

| | |
|------------|------------------------------|
| Dimensions | 40 x 760 mm // 1 9/16 x 30 " |
|------------|------------------------------|

| | |
|------|------|
| Grit | P 80 |
|------|------|

| | |
|------------|----|
| Sales unit | 10 |
|------------|----|