



Cup wheel 80x25x22,23-65x15 C 30 N, stone, cylindrical type

- Surface grind for all stone processing needs
- Hardness: medium
- Resin-bonded
- Good cutting output with good tool life
- Only for dry sanding/grinding
- Maximum working speed 50 m/s
- For angle grinders with grinding wheel Ø 115 mm, 125 mm and 150 mm

Order no.	629175300
EAN code	4007430414748

Diameter x thickness x bore	80 x 25 x 22.23 mm
-----------------------------	-----------------------

Maximum speed	11940 rpm
---------------	-----------

Sales unit / packaging unit	1 / 20
-----------------------------	--------