



Wheel brush 125x0.5x6 /22.23 mm, steel-wire, twisted

- Specially developed for the professional processing of U and V-weld seams in pipeline construction, as well as for root weld seam preparation
- Edging type: twisted steel wire
- Thickness of plait: 6.0 mm

Order no.	626815000
EAN code	4007430296009
Diameter	125 mm / 5 "
Bore Ø	22.23 mm / 7/8 "
Wire thickness	0.50 mm
Maximum speed	12500 rpm
Sales unit / packaging unit	1 / 1