



Small cutting disc 50x2.0x6.0 mm Inox

- High-output disc especially for processing stainless steel
- Maximum cutting output with very long tool life by the use of special corundums. Free from iron, sulphur and chlorine (Fe + S + Cl ≤ 0.1 %), for all rust and acid resistant steels (V2A, Nirosta, INOX), spring steels, tool steels
- For use in the manufacture of vehicles, containers, car bodies, switch cabinets etc. Cutting discs for quiet, precise cutting cuts without burrs
- Hardness: hard

Order no.	630192000
EAN code	4007430097873
Diameter x thickness x bore	50 x 2 x 6 mm // 2 x 1/16 x 1/4 "
Maximum speed	30600 rpm
Maximum working speed	80 m/s
Sales unit / packaging unit	1 / 25