



3 Combinator 76x2.0x10 mm, Inox, cutting and grinding disc, straight version

- One grinding wheel for two applications: quick cutting, as well as easy deburring and sanding
- All-purpose use for processing stainless steel and for general metal processing
- Low in iron, sulphur and chlorine (Fe + S + Cl ≤ 0.1 %)
- Hardness: hard
- Reduces labour costs by saving on set-up time
- Eliminates time-consuming disc change during mobile use
- Highest standards in quality and safety thanks to the dimensional and lateral stability of the disc design (proven safety with 3 full-surface layers of material)
- Maximum working speed: 80 m/s

Order no.	626872000
EAN code	4061792174221
Quality class	A 46-U
Diameter x thickness x bore	76 x 2 x 10 mm // 3 x 1/16 x 3/8 "
Version	straight
Maximum speed	20100 rpm
Sales unit / packaging unit	3 / 1