

Product information

09 12 240 T

Lineman's Pliers

American style

DIN ISO 5746 ASME B107.20



- High transmission ratio for easy cutting
- Requires 50 % less effort compared with conventional combination pliers thanks to optimised transmission ratio
- With fish tape puller in the joint gap
- With universal mandrel crimping point below the joint
- Pliers with tether attachment point for mounting a fall protection system
- Solid construction for heaviest strain; universally applicable
- Ergonomically optimised handle shape for firm contact to the hand and fatigue reducing operation
- Particularly effective cross-hatched knurled gripping zone in the jaws - for strong gripping and pulling
- Additional gripping zone below the joint for powerful leverage and pressing performance
- With cutting edges for soft and hard wire
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Vanadium electric steel, forged, multi stage oil-hardened

General

Article No.	09 12 240 T
EAN	4003773079958
Pliers	black atramentized
Head	polished
Handles	with slim multi-component grips, with integrated tether attachment point for a tool tether
Weight	445 g
Dimensions	240 x 55 x 23 mm
Standard	DIN ISO 5746 ASME B107.20
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities medium hard wire (diameter)	Ø 4.6 mm
Cutting capacities hard wire (diameter)	Ø 3.0 mm
Drop Protection System	yes

technical change and errors excepted

