



## Magnetic drill stand M 100

- Magnet base with high holding power for safe operation
- Also suitable, when used in conjunction with the safety chain supplied, for working on vertical, sloping, or overhead surfaces
- Vertical feed driven by rack and pinion
- In order to position the tip of the drill bit that is fitted in the drill exactly over the punch mark on the material to be drilled, the upper part of the magnetic drill stand can be swivelled and moved sideways
- Power socket on the drill stand for connecting the drill directly
- The drill fitted to the drill stand cannot be started until the drill stand itself has been switched on
- Adjustable support to back up the stand against the high reacting forces that arise when drilling
- Graduated collar indicating the depth to which the hole is drilled
- Can be complemented with the drill B 32/3 to a magnetic drill unit with max. drill diameter 100 mm (with core hole drill).

Order no. EAN code	62710000 4007430185709
Aperture	65 mm
Depth of feed	260 mm / 10 1/4 "
Maximum height	650 mm / 25 19/32 "
Magnetic force (maximum)	18000 N / 1631.4 lbs
Dimensions magnet base	110 x 220 mm // 4 5/16 x 8 21/32 "
Weight	22 kg