



## Saw blade "power cut wood - professional", 152x2.4/1.6x20 Z12 FZ 15°

- For coarse and semi-fine cuts with continuous feed. Ideal for high feed rate / low power consumption machines
- Good cutting results for straight cuts in solid wood
- Partially suitable for construction wood with nails and concrete residue
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel

<b>Order no.</b>	<b>628001000</b>
<b>EAN code</b>	<b>4007430176127</b>
Diameter x cutting width x bore	152 x 2.4 x 20 mm
Material	HW/CT
Number of teeth	12
Tooth shape	FZ
Steel blade thickness	1.6 mm
Rake angle	15°
Suitable for	Ks 0852 S
Packaging	Cardboard box