

## **Product information**

## 36 12 130

## **Electronics Mounting Pliers**



- To bend wire in shape for the distance to the board
- Precision pliers for very fine assembly and repair work in electronics
- For bending and cutting off wire ends on components
- Sturdy, zero backlash box joint
- Smooth ground gripping surfaces
- Edges carefully deburred
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Ball bearing chrome steel, oil hardened

MW

| Ge | neral   |
|----|---------|
| ~~ | IIVI MI |

| General                    |                            |
|----------------------------|----------------------------|
| Article No.                | 36 12 130                  |
| EAN                        | 4003773016861              |
| Head                       | mirror polished            |
| Handles                    | with multi-component grips |
| Weight                     | 70 g                       |
| Dimensions                 | 130 x 68 x 17 mm           |
| REACH compliant            | does not contain SVHC      |
| RoHS compliant             | not applicable             |
| Technical details          |                            |
| Jaw thickness (joint) (T1) | 9.5 mm                     |
| Tips thickness (W4)        | 6.0 mm                     |
| Head width (W3)            | 12.0 mm                    |
| Handle width               | 5.5 mm                     |
| Jaw length (L3)            | 23.0 mm                    |
| Application                | bend wire shape            |

technical change and errors excepted

