



Saw blade "power cut wood - professional", 160x2.2/1.4x20, Z10 WZ 22°

- For coarse and semi-fine cuts with continuous feed. Ideal for high feed rate / low power consumption machines
- Good cutting results for straight cuts in solid wood
- Partially suitable for construction wood with nails and concrete residue
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel

Order no. EAN code	628002000 4007430176134
Diameter x cutting width x bore	160 x 2.2 x 20 mm
Material	HW/CT
Number of teeth	10
Tooth shape	WZ
Steel blade thickness	1.4 mm
Rake angle	22°
Suitable for	KS 54 / KSE 55 Plus / KSE 55 Vario Plus / KS 55 / KS 55 FS / KS 55 / KS 55 FS
Packaging	Cardboard box