



## Saw blade "power cut wood - professional", 190x2.2/1.4x30, Z16 FZ/FA 12°

- For coarse and semi-fine cuts with continuous feed. Ideal for high feed rate / low power consumption machines
- Good cutting results for straight cuts in solid wood
- Partially suitable for construction wood with nails and concrete residue
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel

<b>Order no.</b>	<b>628006000</b>
<b>EAN code</b>	<b>4007430176172</b>
Diameter x cutting width x bore	190 x 2.2 x 30 mm // 7 1/2 x 1/16 x 1 3/16 "
Material	HW/CT
Number of teeth	16
Tooth shape	FZ/FA
Steel blade thickness	1.4 mm
Rake angle	12°
Suitable for	KS 66 / KS 66 Plus / KSE 68 Plus / KS 66 FS
Packaging	Cardboard box