

## Product information

# 64 01 115

## Electronics End Cutting Nipper

DIN ISO 9654




- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The polish or mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 56 HRC
- End Cutter, with small bevel
- Ball bearing chrome steel, oil hardened

### General

Article No.	64 01 115
EAN	4003773017745
Head	mirror polished
Handles	with non-slip plastic coating
Weight	55 g
Dimensions	115 x 63 x 13 mm
Standard	DIN ISO 9654
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

### Technical details

Cutting capacities soft wire (diameter)	Ø 2.0 mm
Cutting capacities medium hard wire (diameter)	Ø 1.0 mm
Cutting capacities hard wire (diameter)	Ø 0.6 mm
Head width (A)	11 mm
Jaw length (B)	6 mm
Jaw thickness (joint) (D)	7.5 mm
Cutting edge length mm (C)	16 mm



technical change and errors excepted

