



Saw blade "precision cut wood - professional", 250x2.8/1.8x30, Z60 WZ 15°

- Very wide range of uses in wood processing
- For very good, clean cutting results for longitudinal or cross-cuts in softwood and hardwood
- Perfectly suited for hard wood and plywood, untreated chipboards, coated or veneered, MDF, composite materials
- High power consumption so the saw must have a high performance motor
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel
- Secondary holder for circular saw blades with Ø 216, 250, 254 and over 300 mm

Order no.	628049000
EAN code	4007430176868
Diameter x cutting width x bore	250 x 2.8 x 30 mm
Material	HW/CT
Number of teeth	60
Tooth shape	WZ
Steel blade thickness	1.8 mm
Rake angle	15°
Suitable for	TS 250 / PKU 250 / PK 255 / PKF 255 / PKF 255 V8 / Multi 260 / Multi 310 / PK 250
Packaging	Cardboard box