



Saw blade "power cut wood - professional", 165x2.0/1.2x20 Z14 FZ/FA 10°

- For coarse and semi-fine cuts with continuous feed. Ideal for high feed rate / low power consumption machines
- Good cutting results for straight cuts in solid wood
- Partially suitable for construction wood with nails and concrete residue
- Particularly long tool life thanks to best carbide quality and finely-ground teeth
- Precise, low-noise and vibration-minimised cuts thanks to lasered expansion slots (and partially laser ornaments) as well as lasered steel blades made from sintered steel

Order no. EAN code	628292000 4061792173712
Diameter x cutting width x bore	165 x 2.2 x 20 mm
Material	HW/CT
Number of teeth	14
Tooth shape	FZ/FA
Steel blade thickness	1.4 mm
Rake angle	10°
Suitable for	KS 18 LTX 57 / KT 18 LTX 66 BL / KS 18 LTX 66 BL
Packaging	Cardboard box