

Product information

77 02 120 H ESD

Electronics Diagonal Cutter with carbide cutting edges ESD

DIN ISO 9654 DIN EN 61 340-5



- For extreme demands on cutting pliers caused by hard or tough materials, e.g. piano, nickel, tungsten and diode wire, such as those used more frequently in the electronics and aerospace industries
- Always the right cutting tool, even with the hardest material
- Precision carbide metal cutting edges soldered into forged blanks
- Sturdy, zero-backlash box joint
- Hardness of the carbide cutting edges 80 – 83 HRC
- Pliers with carbide metal cutting edges have a substantially longer service life than such with conventional cutting edges
- Constantly reliable cutting results due to the avoidance of cutter deformations
- High cost saving due to longer service life of the pliers
- Electrically discharging handles - dissipative




General

| | |
|-----------------|------------------------------|
| Article No. | 77 02 120 H ESD |
| EAN | 4003773075813 |
| Head | mirror polished |
| Handles | with multi-component grips |
| Weight | 85 g |
| Dimensions | 120 x 50 x 19 mm |
| Standard | DIN ISO 9654 DIN EN 61 340-5 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|--|----------|
| Cutting capacities medium hard wire (diameter) | Ø 1.4 mm |
| Cutting capacities hard wire (diameter) | Ø 1.0 mm |
| Cutting capacities piano wire (diameter) | Ø 0.6 mm |
| Cutting capacities soft wire (diameter) | Ø 2 mm |
| Jaw length (B) | 14 mm |
| Jaw thickness (joint) (D) | 7.5 mm |
| Head width (A) | 11 mm |
| ESD | yes |

Technical details



technical change and errors excepted

