



Cup wheel 80x25x22,23-65x15 A 80 M, steel, cylindrical type, pack: 1 pieces

- Surface grind for all metal processing needs
- Hardness: medium
- Resin-bonded
- Good cutting output with good tool life
- Only for dry sanding/grinding
- Maximum working speed 50 m/s
- For angle grinders with grinding wheel Ø 115 mm, 125 mm and 150 mm

Order no.	630727000
EAN code	4007430421531

Diameter x thickness x bore	80 x 25 x 22.23 mm // 5 3/8 x 7/8 x 7/8 "
-----------------------------	---

Maximum speed	11940 rpm
---------------	-----------

Sales unit / packaging unit	1 / 1
-----------------------------	-------