



Geared chuck 20 mm, B 22

- Tried and tested 1000 times
- The chuck for every type of job
- With female thread or female taper for hand-held or fixed drills as well as for hand-held impact drills
- The clamping force remains constant during drilling and impact drilling
- For clockwise rotating drills only

Order no.	635058000
EAN code	4007430427595
Clamping width	5 - 20 mm // 3/16 - 25/32 "
Female thread	B22
Outer Ø	65 mm / 2.56 "
Length (closed)	113 mm / 4.45 "
Weight	0.75 kg
Key size	4