

#### **Product information**

### 77 32 120 H

# **Electronics Diagonal Cutter with carbide cutting edges**

**DIN ISO 9654** 



- · Pointed head with chamfer
- With small bevel
- For extreme demands on cutting pliers caused by hard or tough materials, e.g. piano, nickel, tungsten and diode wire, such as those used more frequently in the electronics and aerospace industries
- Always the right cutting tool, even with the hardest material
- Precision carbide metal cutting edges soldered into forged blanks
- Sturdy, zero-backlash box joint
- Hardness of the carbide cutting edges 80 83 HRC
- Pliers with carbide metal cutting edges have a substantially longer service life than such with conventional cutting edges
- Constantly reliable cutting results due to the avoidance of cutter deformations
- High cost saving due to longer service life of the pliers




General		
Article No.	77 32 120 H	
EAN	4003773075790	
Head	mirror polished	
Handles	with multi-component grips	
Weight	80 g	
Dimensions	120 x 50 x 19 mm	
Standard	DIN ISO 9654	
REACH compliant	does not contain SVHC	
RoHS compliant	not applicable	

Technical details		
Cutting capacities medium hard wire (diameter)	Ø 1.0 mm	
Cutting capacities hard wire (diameter)	Ø 0.6 mm	
Cutting capacities piano wire (diameter)	Ø 0.2 mm	
Cutting capacities soft wire (diameter)	Ø 1.6 mm	
Jaw length (B)	14 mm	
Jaw thickness (joint) (D)	7.5 mm	
Head width (A)	11 mm	

## **KNIPEX** Quality – Made in Germany



### **Technical details**



technical change and errors excepted

