

Product information

79 02 125 ESD

Precision Electronics Side Cutter ESD

DIN ISO 9654 DIN EN 61 340-5



- Round head
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Very precisely ground and sharp cutting edges with very small bevels for exact cutting on delicate electronic components; also available without bevel for flush cutting
- Precision cutting edges additionally induction-hardened, cutting edge hardness approx. 64 HRC
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint with carefully manufactured joint surfaces for even, low-friction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Ball bearing chrome steel, forged, multi stage oil-hardened




General

| | |
|-----------------|------------------------------|
| Article No. | 79 02 125 ESD |
| EAN | 4003773061519 |
| Pliers | burnished |
| Head | polished |
| Handles | with multi-component grips |
| Weight | 61 g |
| Dimensions | 125 x 60 x 20 mm |
| Standard | DIN ISO 9654 DIN EN 61 340-5 |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |

Technical details

| | |
|--|----------------|
| Cutting capacities medium hard wire (diameter) | Ø 1.3 mm |
| Cutting capacities hard wire (diameter) | Ø 0.7 mm |
| Cutting capacities soft wire (diameter) | Ø 0.2 – 1.7 mm |
| Jaw length (B) | 10 mm |
| Jaw thickness (joint) (D) | 6.5 mm |
| Head width (A) | 11 mm |
| ESD | yes |

Technical details



technical change and errors excepted

