

Product information

64 02 115 ESD

Electronics End Cutting Nippers ESD

DIN ISO 9654 DIN EN 61 340-5



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Electrically discharging handles - dissipative
- Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 56 HRC
- Handles with two-colour multi-component grips black/grey
- Ball bearing chrome steel, oil hardened

MM    90°


General

Article No.	64 02 115 ESD
EAN	4003773082231
Head	mirror polished
Handles	with multi-component grips
Weight	70 g
Dimensions	115 x 62 x 17 mm
Standard	DIN ISO 9654 DIN EN 61 340-5
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Cutting capacities soft wire (diameter)	Ø 2.0 mm
Cutting capacities medium hard wire (diameter)	Ø 1.0 mm
Cutting capacities hard wire (diameter)	Ø 0.6 mm
Head width (A)	11 mm
Jaw length (B)	6 mm
Jaw thickness (joint) (D)	7.5 mm
Cutting edge length mm (C)	16 mm
ESD	yes

Technical details



technical change and errors excepted

