

#### **Product information**

### 79 12 125

**REACH** compliant

RoHS compliant

#### **Precision Electronics Diagonal Cutter**

**DIN ISO 9654** 



- Specially for cutting through hard wire and piano wire
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Very precisely ground and sharp cutting edges with very small bevels for exact cutting on delicate electronic components; also available without bevel for flush cutting
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint with carefully manufactured joint surfaces for even, lowfriction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Ball bearing chrome steel, forged, multi stage oil-hardened

General	
Article No.	79 12 125
EAN	4003773071365
Pliers	burnished
Head	polished
Handles	with multi-component grips
Weight	59 g
Dimensions	125 x 59 x 16 mm
Standard	DIN ISO 9654

does not contain SVHC


not applicable

Technical details	
Cutting capacities medium hard wire (diameter)	Ø 1.3 mm
Cutting capacities hard wire (diameter)	Ø 1.0 mm
Cutting capacities piano wire (diameter)	Ø 0.6 mm
Cutting capacities soft wire (diameter)	Ø 0.3 – 1.7 mm
Jaw length (B)	10 mm
Jaw thickness (joint) (D)	6.5 mm
Head width (A)	11 mm

# **KNIPEX** Quality – Made in Germany



## **Technical details**



technical change and errors excepted

