

## **Product information**

## 64 12 115 ESD

## **Electronics End Cutting Nippers ESD**

DIN ISO 9654 DIN EN 61 340-5



- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Electrically discharging handles dissipative
- · Sturdy, zero backlash box joint
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutters additionally laser hardened, cutter hardness at least 56 HRC
- Handles with two-colour multi-component grips black/grey
- Ball bearing chrome steel, oil hardened



General	
Article No.	64 12 115 ESD
EAN	4003773024323
Head	mirror polished
Handles	with multi-component grips
Weight	70 g
Dimensions	115 x 66 x 17 mm
Standard	DIN ISO 9654 DIN EN 61 340-5
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities soft wire (diameter)	Ø 1.4 mm
Cutting capacities medium hard wire (diameter)	Ø 0.8 mm
Head width (A)	11 mm
Jaw length (B)	6 mm
Jaw thickness (joint) (D)	7 mm
Cutting edge length mm (C)	16 mm
ESD	yes

technical change and errors excepted

## **KNIPEX** Quality – Made in Germany





