

Product information

92 37 64

Universal Tweezers

IEC 60900 DIN EN 60900



⚡ 1000 V  $\angle 30^\circ$

- With insulated handles for working on electrical installations: safety up to 1000 V
- For a wide range of requirements and applications in the electronics industry
- Individually tested in accordance with 1000 V EN 60900 / IEC 60900 / VDE and approved for work with voltage up to 1000 Volts
- The insulation is REACH-compliant and free from phthalates that are harmful to health
- Antimagnetic to avoid electromagnetic damage
- High quality stainless steel: extremely tough and very good corrosion resistance against a variety of atmospheric environments and many corrosive materials
- Also available as a set (92 00 04)
- Stainless steel


General

Article No.	92 37 64
Reference number	55015IBK.SA.B.00
EAN	4003773054856
Material	stainless steel
Gripping surfaces	knurled gripping surfaces
Weight	24 g
Dimensions	148 x 14 x 40 mm
Standard	DIN EN 60900 IEC 60900
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details

Finish	angled 30°
Tips width (A)	1 mm
Tips width (B)	1.3 mm
Tweezers tip version	blunt
Corrosion-resistant	yes
Acid resistance	very good
ESD-tested	no
VDE tested	yes
Sectors	Industry electronics
Magnetic	non-magnetisable (80%)
Behaviour	insulated

Technical details



technical change and errors excepted