3M Dual Lock™ Reclosable Fastener SJ3550

Product Data Sheet

January 2017

Supersedes: October 2016

Product Description

3M™ Dual Lock™ Reclosable Fastener SJ3550 is a general purpose black reclosable fastener with 250 stems per square inch. This black fastener has mushroom shaped stems on a polypropylene carrier, which is coated with a white, general purpose acrylic pressure sensitive adhesive.

Key Features

- General purpose acrylic adhesive bonds to medium to high surface energy substrates (e.g. metal, ABS)
- Stem density: 250 stems/in²
- Closure cycle life > 1 000
- Mushroom shaped stems snap in place to ensure fastener is engaged
- Good aging performance and resistance against humidity
- · Good initial adhesion
- Quick and easy to install
- Durable for indoor and outdoor applications

Physical Properties

Туре	SJ3550
Adhesive Type	Acrylic adhesive
Tape Colour	White
Backing	Black polypropylene
Stems	Black polypropylene
Release Liner	3M branded filmic liner
Engaged Thickness acc. DIN EN 1942: 2008	5.4 mm

Performance Characteristics

Туре	SJ3550
90 ° Peel adhesion to Stainless Steel acc. to ISO 29862:2007, 90 ° peel angle @ RT, after 72h @ RT dwell	25 N/cm
90 ° Peel adhesion to PP acc. to ISO 29862:2007, 90 ° peel angle @ RT, after 72h @ RT dwell	4 N/cm
90 ° Peel adhesion to ABS acc. to ISO 29862:2007, 90 ° peel angle @ RT, after 72h @ RT dwell	30 N/cm
90 ° Peel adhesion to Stainless Steel acc. to ISO 29862:2007, 90 ° peel angle @ RT, after 72h @ RT dwell and after 10d @ 38 °C & 98 % rH	23 N/cm
Dyn. Tensile Engagement Strength acc. to ASTM D897-08, tested @ RT	113 N/in²
Dyn. Tensile Disengagement Strength acc. to ASTM D897-08, tested @ RT	231 N/in²
Dyn. Tensile Disengagement Strength acc. to ASTM D897-08, tested @ 70 °C	56 kPa
Dynamic Shear – Max. Force acc.ISO 29863:2007 to stainless steel	102 kPa
Dynamic Shear – Elongation acc.ISO 29863:2007 to stainless steel	60 %
Static Shear Strength Stainless Steel ISO 29863:2007, after 72h @ RT dwell (Holds minimum 77.5 g/cm² for 10.000 minutes)	23 °C – 500 g 70 °C – 500 g
"T" Peel (flexible to flexible) acc. ISO 29862:2007	53 N/cm

Storage & Shelf Life

Store at 16 $^{\circ}$ C - 25 $^{\circ}$ C and 40 - 65 $^{\circ}$ C relative humidity in its original box. The product can be stored up to 24 months after production.

Note: The shelf life may be shortened if the original packaging is not properly sealed or stored in an environment with high temperatures or humidity.

For Additional Information

To request additional product information or to arrange for sales assistance, call......

Address correspondence to: 3M

Important Notice

All statements, technical information and recommendations contained in this document are based upon tests or experience that 3M believes are reliable. However, many factors beyond 3M's control can affect the use and performance of a 3M product in a particular application, including the conditions under which the product is used and the time and environmental conditions in which the product is expected to perform. Since these factors are uniquely within the user's knowledge and control, it is essential that the user evaluate the 3M product to determine whether it is fit for a particular purpose and suitable for the user's method or application. All questions of liability relating to this product are governed by the terms of the sale subject, where applicable, to the prevailing law.

Values presented have been determined by standard test methods and are average values not to be used for specification purposes. Our recommendations on the use of our products are based on tests believed to be reliable but we would ask that you conduct your own tests to determine their suitability for your applications. This is because 3M cannot accept any responsibility or liability direct or consequential for loss or damage caused as a result of our recommendations

3M is a trademark of the 3M Company.

3M Afrique Francophone

Société à responsabilité limitée Au capital de 19.756.400 Dirhams Siège Social: ZF Ksar Almajaz Bureau 6 Plateforme Lot n°2 Immeuble 4 zénith Tanger R.C: 74327, I.F.: 18745050

3M Arabia, LLC

Building 24-25 3M Saudi Arabia Zone C, Business Gate Airport Road Riyadh Saudi Arabia

3M Egypt

Finance Center, New Cairo Plot 140, Banking Sector 5th settlement Cairo Egypt

3M Gulf Limited

Dubai Internet City Building No. 11, 3rd Floor U.A.E

3M Gulf Limited

Ein El Mreisseh Saint Charles City Center, 4th Floor P.O.Box: 11-5025 Riad el Solh Beirut 1107 2180 Lebanon

3M Gulf (Representation Office)

Suhaim Bin Hamad St. Al Mana Towers Tower B, 2nd Floor, Office No.4 Doha Qatar P.O.Box 14684

3M Kenya Ltd

Victoria Towers, 3rd Floor Kilimanjaro Av, Upperhill Kenya

3M Maroc

Société à responsabilité limitée Au capital de 18.000.000 de Dirhams Siège Social: 33, lot la colline II Sidi Maarouf -Casablanca R.C:78517, I.F.: 1084514 Morocco

3M Minnesota Mining and Manufacturing Nigeria Limited

No 2 Sheraton Opebi Link Road Ikeja Lagos Nigeria

3M Pakistan

Islamic Chamber of Commerce Building ST-2/A, Block 9, KDA Scheme 5, Clifton, Karachi Pakistan

3M South Africa and Sub-Saharan Africa

146A Kelvin Drive Woodmead Sandton South Africa