



GVB 18 LTX BL 11-7 HT

- Powerful cordless die grinder with long grinding spindle also for demanding grinding applications, also in hard-to-reach places
- High torque also with low speeds, therefore ideal for working with flap grinding wheels
- Variable speed setting for working with different materials
- Particularly slim handle area for optimum handling and low-fatigue working
- Spindle lock for simple change of tools
- High degree of user safety thanks to fast brake for quick stop of the tool being used (< 1 sec)
- Powerful like a 1,100 Watt mains-powered tool thanks to efficient, service-free Brushless motor
- Electronic overload protection, soft start and restart protection
- Rubber cap for comfortable and safe working
- Battery pack can be rotated in 90° steps for best ergonomics in any working position
- Easy-to-clean dust protection filter protects motor from coarse particles
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	600829850
EAN code	4061792247338
Battery voltage	18 V
No-load speed	1500 - 7000 rpm
Collar diameter	43 mm / 1 11/16 "
Collet chuck bore	6 mm / 0.2362 "
Weight without battery pack	1.5 kg / 3.3 lbs
Weight with battery pack	2.2 kg / 4.9 lbs

Scope of delivery

Collet 6 mm, Protective rubber cap, Dust protection filter, Open-jawed spanner, without battery pack, without charger