

Product information

79 22 120

Precision Electronics Diagonal Cutter

DIN ISO 9654




- Mini-head
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Very precisely ground and sharp cutting edges with very small bevels for exact cutting on delicate electronic components; also available without bevel for flush cutting
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint with carefully manufactured joint surfaces for even, lowfriction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Ball bearing chrome steel, forged, multi stage oil-hardened

General

MM I

Article No.	79 22 120
EAN	4003773061427
Pliers	burnished
Head	polished
Handles	with multi-component grips
Weight	57 g
Dimensions	120 x 71 x 19 mm
Standard	DIN ISO 9654
REACH compliant	does not contain SVHC
RoHS compliant	not applicable
Technical details	
Cutting capacities medium hard wire (diameter)	Ø 0.8 mm
Cutting capacities soft wire (diameter)	Ø 0.1 – 1.3 mm
Jaw length (B)	6.5 mm
Jaw thickness (joint) (D)	6.5 mm
Head width (A)	9 mm



technical change and errors excepted

KNIPEX Quality – Made in Germany



