



ASA 30 L PC with manual filter cleaning

- Compact vacuum cleaner of dust class L with integrated filter cleaning for versatile application
- Fast coupling of metaBOXes with tools and accessories on the vacuum cleaner for easy change of location
- Compact vacuum cleaner for liquids and dry solids with commercial registration
- For extraction from power tools and to clean construction sites, workshops etc.
- Power socket for a power tool for using the automatical-start-up/shut-down of the vacuum cleaner
- PressClean: manual filter cleaning using strong air flow by activating the switch on the extraction unit during breaks
- User protection: certified in accordance with EU standard for L class dust
- Suction stop when vacuuming liquids once the maximum fill level is reached
- Automatic trailing mechanism for emptying the suction hose completely
- Antistatic basic equipment prevents static charge when using appropriate accessories
- Easy transport thanks to cable and hose bracket as well as case for pipes and nozzles
- Practical accessory case and storage area
- Practical accessory accessory box with flip lid for small parts
- Supplied vacuum cleaner accessories with quick system for fast retrofitting when in use

Order no.	60208600
EAN code	4061792230743

Air output max.	4200 l/min / 148 cfm
Vacuum	225 hPa (mbar) / 3.3 psi
Filter surface	3500 cm ² / 542 sq.inch
Input power max.	1200 W
Container volume	30 l / 8 gal
Suction hose Ø	32 mm / 1 1/4 "
Hose length	3.2 m / 10.5 ft
Weight	10.8 kg / 23.8 lbs
Cable length	5.5 m / 18 ft

Scope of delivery

Suction hose Quick (Ø 32 mm / 3.2 m), Coupling bush Quick Ø 28/35 mm, Handle adapter Quick Professional, 3 Plastic suction tubes, Fleece filter bag, Crevice nozzle, Floor nozzle (300 mm wide), Suction nozzle (120 mm wide)