

## **Product information**

## 79 42 125 Z

## **Precision Electronics Diagonal Cutter**

**DIN ISO 9654** 




- For an optimised flush cutting result of soft materials
- For installations with tight tolerances, for precise configuration of wire
- Precision pliers for ultra fine cutting work, e. g. in electronics and fine mechanics
- Very precisely ground and sharp cutting edges with very small bevels for exact cutting on delicate electronic components; also available without bevel for flush cutting
- Cutting edges additionally induction-hardened, cutting edge hardness approx. 62 HRC
- Approx. 20% lighter than conventional electronics pliers
- Bolted joint with carefully manufactured joint surfaces for even, lowfriction movement throughout the entire opening range
- Smooth-running double spring for a gentle and even opening
- Ergonomically optimised multi-component handles
- Ball bearing chrome steel, forged, multi stage oil-hardened

0	
	Cu/soft Ø 0,1-1,3
M	

General	
Article No.	79 42 125 Z
EAN	4003773078449
Pliers	burnished
Head	polished
Handles	with multi-component grips
Weight	58 g
Dimensions	125 x 60 x 19 mm
Standard	DIN ISO 9654
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

Technical details	
Cutting capacities soft wire (diameter)	Ø 0.1 – 1.3 mm
Jaw length (B)	11 mm
Jaw thickness (joint) (D)	6.5 mm
Head width (A)	11 mm



technical change and errors excepted

## **KNIPEX** Quality – Made in Germany



