



## RSEV 19-125 RT + ASR 35 M ACP Set

- System solution for spot sanding of hard materials with diamond cup wheels with effective extraction for optimum work results
- Renovation grinder RSEV 19-125 RT: for effective spot sanding and removal of concrete, screed and coatings with diamond cup wheels.
- All-purpose vacuum cleaner ASR 35 M ACP for extraction on power tools in continuous use on construction sites and in the workshop. AutoCleanPlus: cost and time savings due to automatic MPulse filter cleaning in continuous use. If the optimum suction performance falls below a certain level, the filters are vibrated immediately. Especially suited for extracting concrete and rock dust. High user safety: certified according to EU standard for dust class M dust.

Order no.  
EAN code

691001000  
4007430315984

### Scope of delivery

Renovation Grinder RSEV 19-125 RT: diamond cup wheel concrete "professional", bar handle. All-purpose vacuum cleaner ASR 35 M ACP: antistatic suction hose (Ø 35 mm / 4 m long), handle adapter, connecting sleeve Ø 41/48 mm, 2 plastic suction tubes, 2 polyester filter cassettes (class M), PE filter bags, crevice nozzle, floor nozzle (300 mm wide)

**All-Purpose Vacuum Cleaner ASR 35 M ACP**



Air output max.	4380 l/min / 157 cfm
Vacuum	270 hPa (mbar) / 3.6 psi
Filter surface	8600 cm <sup>2</sup> / 1333 sq.inch
Input power max.	1400 W
Container volume	35 l / 9 gal
Suction hose Ø	35 mm / 1 3/8 "
Hose length	4 m / 15 ft
Weight	16 kg / 35.3 lbs
Cable length	8 m / 26 ft
	<ul style="list-style-type: none"> <li>• For extraction from the power tool in continuous mode, both on construction sites and in the workshop</li> <li>• Especially suited for extracting concrete and rock dust</li> <li>• Compact vacuum cleaner for liquids and dry solids with commercial registration</li> <li>• Power socket for a power tool for using the automatic start-up/shut-down of the vacuum cleaner</li> <li>• AutoCleanPlus: saves both costs and time thanks to automatic MPulse filter cleaning during continuous use</li> <li>• If the optimum suction performance falls below a certain level, the filters are vibrated immediately</li> <li>• High user protection: certified in accordance with EU standard for M class dusts</li> <li>• Automatic shut-down when vacuuming liquids once the maximum fill level is reached</li> <li>• Warning signal on shortfall of the minimum volume flow to protect the user</li> <li>• Optimum suction power by preselection of the hose diameter</li> <li>• Automatic trailing mechanism for emptying the suction hose completely</li> <li>• Antistatic basic equipment prevents static charge when using appropriate accessories</li> <li>• Sturdy thanks to especially large wheels and castors with wheel stop</li> <li>• Cable winding mechanism</li> <li>• Practical accessory case and storage area</li> </ul>

**Renovation Grinder RSEV 19-125 RT**



Cup wheel Ø	125 mm / 5 "
Torque	5 Nm / 44 in-lbs
No-load speed	3800 - 8200 rpm
Rated input power	1900 W
Output power	1240 W
Speed at rated load	6800 rpm
Spindle thread	M 14
Weight (without power cable)	3.5 kg / 7.7 lbs
Cable length	4 m / 13 ft

- For effective spot grinding and removal of concrete, screed and coatings with diamond cup wheels
- Maximum productivity thanks to 1,900 Watt strong Metabo Marathon-motor with low weight
- High torque and overload capacity for demanding applications in continuous use
- Low weight, ideal for sanding walls and ceilings
- Perfect ergonomics thanks to slim handle for maximum control and easy working overhead
- Working close to edges thanks to integrated folding segment
- Optimum extraction results: spring-mounted brush rim at the protective cover that adapts to any surface and segment height
- Front handle for safe and uniform guidance when polishing, adjustable without tools
- Vario Tacho Constamatic (VTC) Full-wave Electronics with Thumbwheel: for working at customised speeds to suit the application material and speeds that remain almost constant, even under load
- Electronic soft start for smooth start-up
- Restart protection: prevents unintentional start-up after power supply interruption
- Metabo S-automatic safety clutch: mechanical decoupling of the drive for safe working should the tool stop unexpectedly
- Connection for dust extraction Ø 35/41 mm