

Product information

92 11 01

Cutting Tweezers




- For particularly demanding precision work: made from high-quality, martensitic hardened steel, tough and highly resistant to corrosion
- Stainless steel with a slim, tapered design for maximum precision when cutting, dissecting and segmenting extremely small objects in tight spaces
- For the electronics industry, as well as repairs and handicrafts
- Mainly used for cutting soft copper, gold or silver wires, as well as magnetic wires
- With extremely hard and sharp oblique cutting nippers
- Also available as an ESD-version: with black epoxy resin coating and a surface resistance between 10⁴ and 10⁹ ohms
- ESD version only: this allows to compansate in a controlled manner the differences in potential between the operator and electronic components
- Stainless steel

General

| General | |
|-------------------|-----------------------|
| Article No. | 92 11 01 |
| Reference number | 15AGW.S.0 |
| EAN | 4003773085003 |
| Material | stainless steel |
| Weight | 25 g |
| Dimensions | 115 x 11 x 15 mm |
| REACH compliant | does not contain SVHC |
| RoHS compliant | not applicable |
| Technical details | |
| Surface | matt finish |
| Finish | bent |
| Tips width (A) | 4.75 mm |
| Tips width (B) | 10 mm |

| Tweezers tip version | Cutting Edges |
|----------------------|----------------------|
| Corrosion-resistant | yes |
| ESD-tested | no |
| VDE tested | no |
| Sectors | Industry electronics |



technical change and errors excepted