



AS 18 L PC Set with trolley

- Light, compact cordless vacuum cleaner for mobile use for extraction and vacuuming of dust and chips
- User safety: certified in accordance with EU standard for dust class L
- PressClean: manual filter cleaning using strong air flow by activating the switch on the extraction unit during breaks
- Eco mode for longer runtime per battery pack charge, boost mode for maximum power
- With integrated blow function for blowing out, drying and drawing off exhaust air
- Large corner switch for easy switching On/Off also by foot
- With stretchy hose for comfortable handling and maximum freedom of movement when vacuuming
- Practical storage for second battery pack, charger, nozzles and hose
- Compact MetaLoc design for stacking with the MetaLoc cases
- Robust housing with rubber protectors at the footprint for gentle, non-slip putting down
- Easy transport with ergonomically-designed handle or carry strap
- Trolley for maximum mobility when working
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	69106000
EAN code	400743033339

Type of battery pack	LiHD
Battery voltage	18 V
Air output max.	2100 l/min / 74 cfm
Vacuum	120 hPa (mbar)
Filter surface	3600 cm ²
Container volume	7.5 l
Suction hose Ø	32 mm
Hose length	3.5 m
Weight without battery pack	6.9 kg / 15.2 lbs
Weight with battery pack	7.5 kg / 16.5 lbs

Scope of delivery

Stretchy suction hose (Ø 32 mm / 0.7-3.5 m), Fleece filter bag, Suction nozzle (120 mm wide), Crevice nozzle, Carrying strap, Trolley, without battery pack, without charger