



TS 254 M Set with TSU stand and TS sliding table

- Compact mobile table saw with impressive cutting performance and high comfort for working
- Anti-twist tubular frame construction for highest demands on the building site and during installations
- Cables and all add-on components for transport can be stored on the casing
- Powerful motor with electronic overload protection
- Motor brake for quick stop of the saw blade in 3 seconds
- Restart protection: prevents unintentional start-up after power supply interruption
- Soft start for long service life of motor and drive
- Precisely adjustable parallel guide / rip fence with double clamping and quick fastening
- Precise saw blade inclination via gear guide
- Automatic resetting to 0 – 45 ° after undercuts
- Easy saw blade change with spindle lock
- Splitting wedge can be lowered without tools for hidden cuts and transport
- Precise, extendable table width extension for extra large working surfaces

Order no.	691190000
EAN code	4061792197404
Dimensions	669 x 748 x 334 mm // 26.343 x 29.437 x 13.156 "
Working height	860 / 334 mm // 33.88 / 13.15 "
Cutting height	0 - 80 mm // 0 - 3.15 "
Maximum cutting height 90/45°	80 / 48 mm // 3.15 / 1.87 "
Maximum cutting width at rip fence	520 mm / 20.46 "
Maximum material width at mitre fence	195 mm / 7.68 "
No-load speed	4200 rpm
Cutting speed	56 m/s / 184 ft/s
Saw blade	254 x 30 mm // 10 x 1.181 "
Saw blade swivel range	-1.5 - 46.5 °
Rated input power S1 100%	1500 W
Weight	24.4 kg / 54 lbs
Cable length	2.3 m / 90.565 "

Scope of delivery

Carbide saw blade with alternately bevel-ground tips (40 teeth), TSU Stand, Rip Fence, Mitre Fence, Sliding table TS, Table Length Extension, Table width extension (right), Push stick