

## Product information

# 92 89 03

### Exchangeable ESD tips

For 92 81 03



- For particularly demanding precision work: tough and highly resistant to corrosion
- Maximum surface protection when handling sensitive electronic components, micro-mechanical parts, as well as glass and ceramic components
- For the electronics and precision engineering industries, watchmakers and jewellers
- Handcrafted body: polished edges and an excellent matt, scratch-free and non-reflective surface
- High-quality premium stainless steel body: high temperature resistance and excellent corrosion resistance to most chemicals, salts and acids
- The interchangeable tips are made from 30% carbon fibre reinforced plastic: very good electrical and thermal conductivity, scratch-proof and with high abrasion resistance
- The interchangeable, carbon fibre reinforced plastic tips have a surface resistance between  $10^2$  and  $10^4$  ohms to compensate in a controlled manner the differences in potential between the operator and electronic components
- The interchangeable tips are permanently temperature stable up to  $130^\circ\text{C}$ , and up to  $190^\circ\text{C}$  for short periods
- The carbon fibre reinforced plastic tips are extremely flexible, fatigue-resistant, vibration-dampening and water-repellent
- The tips have good chemical resistance to most oils, lubricants, fuels and nonpolar solvents
- The same accuracy and stability as regular tweezers: the plastic tips have a 3-point connection with zero backlash (2 fixed points on the arms, one screw), which guarantee the user perfect attachment to the body with zero backlash
- Potential savings: the tip assortment includes a selection of the most diverse shapes. Depending on the application, only the tips need to be purchased later


#### General

Article No.	92 89 03
Reference number	A7CF
EAN	4003773087144
Gripping surfaces	smooth gripping surfaces
Weight	1 g
Dimensions	40 x 15 x 3.5 mm
REACH compliant	does not contain SVHC
RoHS compliant	not applicable

#### Technical details

Surface	matt finish
Tips width (A)	0.4 mm
Tips width (B)	0.7 mm
Corrosion-resistant	yes
Acid resistance	very good
ESD-tested	yes
VDE tested	no
Sectors	Industry electronics
Magnetic	non-magnetisable (100%)
Behaviour	electrically dissipative

## Technical details



*technical change and errors excepted*