



Set SXA 18 LTX 125 BL + AS 18 L PC Compact

- Cordless random orbital sander SXA 18 LTX 125 BL: Flat cordless random orbital sander with ergonomic design and low weight for low-fatigue working. Comfortable guidance of the sander close to the surface thanks to the low overall height. Low-vibration working thanks to smooth running operation.
- Cordless vacuum cleaner AS 18 L PC Compact: Portable, compact cordless vacuum cleaner for wet and dry vacuum cleaning (IPX4), ideal for smaller cleaning and extraction jobs. Commercially approved cordless vacuum cleaner, certified for dusts of dust class L. PressClean: manual filter cleaning using strong air flow by activating the switch on the extraction unit during breaks. With integrated blow function: for blowing out, drying and drawing off exhaust air.

Order no.
EAN code

69119900
4061792202849

Scope of delivery

Cordless random orbital sander SXA 18 LTX 125 BL, metaBOX 215, dust bag, hook and loop sanding sheet, cordless vacuum cleaner AS 18 L PC Compact, stretch suction hose, 3 plastic suction tubes, fleece filter bag, suction nozzle (120 mm wide), crevice nozzle, carry strap, without battery pack, without charger

Cordless random orbital sander SXA 18 LTX 125 BL



Battery voltage	18 V
Diameter of backing pad	125 mm / 5 "
No-load speed	4000 - 10000 rpm
Orbital frequency with no load	8000 - 20000 rpm
Orbit diameter	2 mm
Weight without battery pack	1.1 kg
Weight with battery pack	1.5 kg
	<ul style="list-style-type: none"> • Flat cordless random orbital sander with ergonomic design and low weight for low-fatigue working • Comfortable guidance of the sander close to the surface thanks to the low overall height • Low-vibration working thanks to smooth running operation • Grip area with non-slip soft-grip surface • Soft start minimises surface damage when placing the machine on the work surface • Unique Metabo brushless motor highest efficiency when grinding, also in continuous mode • Infinitely variable speed control for working with different materials • Multi-hole sanding pad for effective extraction and a longer service life of the sanding medium • With easy to empty textile dust bag for working without extraction facilities • Can be connected to an all-purpose vacuum cleaner with the coupling bush 630798000 • Motor and plate brake permits quick placing down of the machine after use • Removable protector protects adjacent surfaces and increases the service life of the sanding pad • With attachment point for tool safety straps for working at great heights

Cordless vacuum cleaner AS 18 L PC Compact



Battery voltage	18 V
Air output max.	2100 l/min
Vacuum	120 hPa (mbar)
Filter surface	3000 cm ²
Container volume	6 l
Suction hose Ø	32 mm
Hose length	2.5 m
Weight without battery pack	3.8 kg
Weight with battery pack	4.8 kg
	<ul style="list-style-type: none"> • Portable, compact cordless vacuum cleaner for wet and dry vacuum cleaning (IPX4), ideal for smaller cleaning and extraction jobs • User safety: certified in accordance with EU standard for dust class L • PressClean: manual filter cleaning using strong air flow by activating the switch on the extraction unit during breaks • Eco mode for longer runtime per battery pack charge, boost mode for maximum power • With integrated blow function for blowing out, drying and drawing off exhaust air • With stretchy hose for comfortable handling and maximum freedom of movement when vacuuming • Dust-proof and splash-proof battery pack compartment with lockable flap • Hoses, pipes and nozzles can be stored directly on the vacuum cleaner • Easy transport with ergonomically-designed handle or carry strap • Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com