

Product information

97 53 09

Self-Adjusting Crimping Pliers for wire • ferrules

With front loading




- Compression from 0.08 10.0 and 16.0 mm² in one profile
- With selector lever for setting the crimping area either to 0.08 10 mm² or 16 mm²
- Also suitable for twin wire ferrules up to 2 x 10 mm², but smaller than Ø 6.6 mm (e.g. KNIPEX art. no. 97 99 377)
- For crimping wire ferrules according to DIN 46228 parts 1 + 4
- Self-adjusting adaptation to the desired wire ferrule size: no wrong crimps caused by using the wrong die
- Frontal insertion of the wire ferrules into the pliers
- Repetitive, high crimping quality due to ratchet mechanism (unlockable)
- Tools have been set precisely (calibrated) in the factory
- Optimum transmission of force thanks to toggle lever for fatiguereduced operation
- Handy shape and low weight provide high operation comfort
- Special quality chrome vanadium electric steel, oil-hardened



General	
Article No.	97 53 09
EAN	4003773044550
Pliers	burnished
Handles	with multi-component grips
Weight	486 g
Dimensions	190 x 20 x 23 mm
REACH compliant	contains SVHC
RoHS compliant	not applicable

Technical details



technical change and errors excepted






































97 53 08: lateral loading of wire ferrules up to 2.5 mm² parallely from the side e.g. in confined areas







Front loading of wire ferrules e.g. in switchboards





Square-Crimp