

Product information

99 10 250

High Leverage Concreters' Nipper

High lever transmission

DIN ISO 9242



- 25 % less effort required compared to conventional concreters' nippers of the same size
- Extra-slim form for tying deep mounted steel rods
- To lace concrete reinforcing steel with binding wire from a roll
- Wire is twisted and cut in a single pass
- High-leverage joint, minimising strain, even when thick binding wires are used
- The high damping of the cutting stroke on cutting through the binding wire reduces the strain on tendons and muscles
- Cutting edges additionally hardened; cutting edge hardness approx.
 61 HRC
- High-grade special tool steel, forged, multi stage oil-hardened

General

99 10 250
4003773071396
black atramentized
polished
350 g
250 x 49 x 25 mm
DIN ISO 9242
does not contain SVHC
not applicable
Ø 1.8 mm
Ø 3.3 mm
23.0 mm 25.0 mm

technical change and errors excepted