

TECHNICAL DATA SHEET

IAN XXTP Pro BOA® blue AIR ESD S1PS No. 721341


Sz. 35 - 49



LABELLING ACCORDING TO STANDARD

| | |
|---|---|
| Standard for safety footwear EN ISO 20345:2022 S1PS | Basic requirement for S1PS: A Antistatic shoe - E Energy absorption in the heel - P Steel midsole - S Textile penetration protection - Closed heel area - Basic Slip resistance test on ceramic tile + NaLS (soap solution) |
| Additional requirements | FO FUEL RESISTANCE SR Slip resistance on ceramic tile with glycerine. |



FORM





| | |
|--|--|
| Safety sandal  | Form A - in size 42, the upper height must not exceed 11.2 cm. |
|--|--|

AREAS OF APPLICATION

| | |
|----------------------|---|
| Areas of application | Areas where there is a risk of electrostatic discharge (ESDS/ESD) |
|----------------------|---|

FEATURES

| | | |
|--|--|---|
| ESD equipment | Thanks to its excellent discharge capability, the shoe is suitable for work in ESD sensitive or electrostatically protected areas (EPA). The shoes comply to the standard 61340-5-1. |  |
| Sizes (unisex model) | <ul style="list-style-type: none"> Expanded size range: available in sizes 35 - 49 | |
| Certification in accordance with DGUV rule 112-191 | <ul style="list-style-type: none"> Certified for orthopaedic inserts |  |
| Padded upper edge | <ul style="list-style-type: none"> Excellent wearing comfort: the padded upper edge protects the Achilles tendon. | |
| Padded tongue | <ul style="list-style-type: none"> Excellent wearing comfort: The tongue prevents pressure marks. | |

| FEATURES | |
|---|---|
| Reflective material | <ul style="list-style-type: none"> • Good visibility in the dark  |
| Sole core made of Infinergy® by BASF  | <p>The sole core consists of expanded, thermoplastic polyurethane in the form of oval foam beads. These stick together and are very light and elastic. This revolutionary technology cushions the impact and bounces back extremely well on pressure, so that the energy can be returned to the wearer. Even under low temperatures of -20 °C, the core maintains its high elasticity.</p>  |
| BOA® Fit System | <p>Delivering fit solutions purpose-built for performance, the BOA® Fit System is featured in products across industries (including sports, workwear and medical) and consists of three integral parts: a micro adjustable dial, a super-strong lightweight lace and low friction lace guides. Each unique configuration is engineered for fast, effortless, precision fit and is backed by the BOA® Guarantee.</p>  |
| Leather-free equipment | <ul style="list-style-type: none"> • Suitable for persons allergic to leather |
| TPU scuff cap | <ul style="list-style-type: none"> • Excellent wear protection in the shoe tip • Protects the upper leather in this area against premature wear |
| UPPER MATERIAL | |
| Microfibre | <ul style="list-style-type: none"> • Synthetic material • Particularly soft • Retains its shape • Tear-resistant • Quick drying • Abrasion-resistant and light |
| Textile material | <ul style="list-style-type: none"> • Areas of application S1 • Synthetic material • Retains its shape • Tear-resistant • Quick drying • Abrasion resistant and light |
| LINING | |
| Breathable fabric lining | <ul style="list-style-type: none"> • Climate-regulating • Good ventilation • Skin-friendly • High absorption and emission of moisture |
| Heel pocket lining | <ul style="list-style-type: none"> • The abrasion-resistant microfibre material is particularly sturdy and provides for a pleasant wearing comfort. |

TOE PROTECTION CAP

Composite toe cap



- Protection against impacts of min. 200 joules and pressure loading of min. 15 kN
- Permanent edge coverage for cushioning
- Ergonomically shaped
- Comfortable toe room
- Good coverage of the little toe area
- Low weight - weighs less than conventional steel caps
- 100% metal-free
- 100% anti-magnetic

INLAY SOLE

Full-length inlay sole
ESD PRO



- ESD EQUIPMENT: Protection against electrostatic discharge (ESD). The full-length, exchangeable inlay sole is conductive and designed for the use in ESD safety footwear according to the standards DIN EN ISO 20345 and DIN EN 61340-5-1.
- The full-length, exchangeable inlay sole provides the highest possible comfort in safety shoes.
- The inlay sole is functionally absorbing and releasing moisture and thus provides for a pleasant foot climate.
- The extreme softness of the PU foam absorbs shocks on impact and increases walking comfort.
- Improvement of the shoe climate thanks to the PU foam's open cell structure. So the foot is always kept comfortably dry.

PENETRATION RESISTANCE

Metal-free penetration
protection

The textile midsole complies with the penetration safety standard EN 12568 and furthermore fulfils the additional requirements for penetration protection in accordance with EN ISO 20344 / 20345. The light and flexible material enables an increased elasticity of the shoe, which can particularly be recognized when working on uneven grounds or on your knees.

The textile variant offers 100 % foot coverage compared to steel midsoles (foot coverage 85 % due to limits in the shoe manufacturing process). Being 100 % metal-free and antimagnetic, this equipment is used as penetration protection in safety shoes.

OUTSOLE

WELLMAXX TRAINERS
POWER double-density
sole with profile



- Excellent slip resistance
- Antistatic

Outsole: TPU (thermoplastic polyurethane)

- Colour: blue, with coloured inserts
- Profile depth: 3.5 mm
- Abrasion-resistant
- Heat-resistant to approx. 130°C
- Flexible at cold temperatures to approx. -20°C
- Oil and fuel resistant

Midsole: PU (polyurethane) with a core made of Infinergy® by BASF

- The soft PU core provides a good impact absorption and high wearing comfort
- The core made of Infinergy® provides a very good cushioning with rebound effect