



TE 24-230 MVT CED with diamond cutting disc UP

- Powerful diamond cutter for low-dust dry cuts up to 60 mm in mineral materials
- Best view on the cutting line thanks to the open design of the dust extraction shroud
- Efficient dust extraction for health protection and clean construction sites
- Fast work progress and long service life thanks to powerful Metabo Marathon-motor
- Ideal for precise, horizontal cutting thanks to pushing cut; conversion to pulling cut possible
- Precise cuts on even surfaces thanks to metal base plate with rollers
- Safety and control in any situation: Soft start, Metabo Vibra-Tech (MVT) vibration damping, electronic safety shutdown and restart protection
- Robust die-cast aluminium dust extraction shroud with tool-free setting of the cutting depth
- Auto-stop carbon brushes to protect the motor
- Connection for dust extraction \varnothing 35/41 mm

Order no.	600434500
EAN code	4061792122291
Cutting disc \varnothing	230 mm / 9 "
Max. cutting depth	60 mm / 2 3/8 "
Rated input power	2400 W
Output power	1600 W
No-load speed	6600 rpm
Spindle thread	M 14
Weight (without power cable)	8.1 kg / 17.9 lbs
Cable length	4 m / 13 ft

Scope of delivery

Extraction hood CED 230, Diamond cutting disc UP, Flat-pin spanners, Inner support flange, Spacer Rings, Nut with two holes, Side handle, Plastic carry case