



## AS 20 L PC with manual filter cleaning

- Compact vacuum cleaner of dust class L with integrated filter cleaning for versatile application
- Compact vacuum cleaner for liquids and dry solids with commercial registration
- Ideal for mobile use due to low weight and compact construction
- For extraction from power tools and to clean construction sites, workshops etc.
- PressClean: manual filter cleaning using strong air flow by activating the switch on the extraction unit during breaks
- User protection: certified in accordance with EU standard for L class dust
- Suction stop when vacuuming liquids once the maximum fill level is reached
- Practical accessory box with flip lid for small parts
- Supplied vacuum cleaner accessories with quick system for fast retrofitting when in use

Order no. EAN code	602083000 4061792230675
Air output max.	4200 l/min / 148 cfm
Vacuum	225 hPa (mbar) / 3.3 psi
Filter surface	3500 cm <sup>2</sup> / 542 sq.inch
Input power max.	1200 W
Container volume	20 l / 5 gal
Suction hose Ø	32 mm / 1 1/4 "
Hose length	1.75 m / 6 ft
Weight	9.4 kg / 20.7 lbs
Cable length	5.5 m / 18 ft

### Scope of delivery

Suction hose Quick (Ø 32 mm, 1.75 m), Hard cone sleeves Quick, 3 Plastic suction tubes, Fleece filter bag, Crevice nozzle, Floor nozzle (300 mm wide), Suction nozzle (120 mm wide)