


**Transport equipment**

## Product data sheet

Article no.: 9400B ESD-Table top cart with platforms made of sheet steel



Electrostatic discharge construction (ESD = Electrostatic Discharge). Tubular steel and sectional steel welded, conductive powder coating, slate grey. Screw and plug type construction. 2 electrically conductive platforms made of steel sheet, flush with frame, powder coated. 2 swivel and 2 fixed-wheel castors. Wheels electrically conductive (anti-static) with TPE-ESD tyres (thermoplastic elastomer). Hubs with precision deep groove ball bearing. Maximum comfort: Very low starting, rolling and swivelling resistance. Low noise operation on level floors. Tyres are non-marking. Castors with wheel lock, according to the European Standard EN 1757-3 (safety of platform trolleys). Capacity of upper shelf 200 kg.

### Technical Details:



<b>Total load capacity (kg)</b>	500
<b>Length of usable platform (mm)</b>	850
<b>Width of usable platform (mm)</b>	500
<b>Shelf heights (mm)</b>	228, 860
<b>Total length (mm)</b>	1047
<b>Total width (mm)</b>	509
<b>Total height (mm)</b>	860
<b>Tyres</b>	TPE-ESD
<b>Wheel size (mm)</b>	160 x 40
<b>Weight (kg)</b>	47
<b>Country of origin</b>	Germany
<b>Warranty (years)</b>	10
<b>Customs tariff number</b>	87168000
<b>GTIN</b>	4017976394008