# KERN ABT 120-4NM

## The premium model with single-cell weighing system





Category	
Brand	KERN
Product categoriy	Laboratory balance
Product group	Analytical balance
Product family	ABT
Measuring System	
Conformity assessment possible	✓
Construction type of the scale	Single-range balance
Weighing system	Single-Cell
Weighing capacity [Max]	120 g
Weighing capacity [Max] (ct)	600 ct
Readability [d]	0,0001 g
Readability carat [d] (ct)	0,001 ct
Resolution	1.200.000
Linearity	± 0,0002 g
Reproducibility	0,0001 g
Tare range	120 g
Default unit	g
Units	g ct
Units (if device is conformity	g
assessed)	ct
Minimum weight [Min]	0,01 g
USP Minimum weight of sample (k = 2, U = 0.1%)	200 mg
Minimum weight [Min] (ct)	0,1 ct
Adjustment options	Adjusting with external weight Internal calibration (automatic) Adjusting with internal weight (manual)

Automatic adjustment - Standard	0,5 °C
temperature deviation	
Automatic adjustment - Standard time interval	4 h
Stabilization time	4 s
Warm-up time	8 h
Eccentric loading at 1/3 [Max]	0,0005 g
Approval	
CE mark	1
Pattern approval for conformity	1
assessment	v
Accuracy classe	
Verification scale interval [e]	0,001 g
Verification scale interval [e] (ct)	0,01 ct
Conformity assessment possible ex works	$\checkmark$
ex works	
Display	
Display type	LCD
Display digit height	14 mm
Construction	
Dimension housing (W×D×H)	217×356×338 mm
Dimensions rectangular draught shield - inner (W×D×H)	168×172×223 mm
Dimensions rectangular draught shield - outer (W×D×H)	200×240×260 mm
Material display housing	Plastics
Material housing	metal
Material weighing plate	stainless steel
Material draught shield	glass
Dimensions weighing surface (Ø)	80 mm
Levelling feet adjustable	$\checkmark$
Functions	
Number of keys for operation	6
Capacity display	1
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Function for averaging under unstable weighing conditions	1
Standby function	1
Recipe/summing level	Rez A (Net total)
Sum memory function	1
Underfloor weighing	Hook (included in delivery)

# KERN ABT 120-4NM



The premium model with single-cell weighing system

Interfaces	RS-232 standard
Counting	
Smallest piece weight when piece counting - laboratory conditions	1 mg
Smallest piece weight when piece counting - normal conditions	10 mg
Counting reference weight can be entered	1
Reference quantity	10, 20, 50, 100
Counting resolution (laboratory conditions)	120.000

## Power Supply

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	12 V DC, 1000 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH

### Environmental conditions

Humity of environment [Max]	80 %	
Ambient temperature [Min]	10 °C	
Ambient temperature [Max]	30 °C	
Storage temperature [Min]	-10 °C	
Storage temperature [Max]	50 °C	

### Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	590×400×540 mm
Net weight	7 kg
Shipping method	Parcel service
Net weight approx.	7 kg
Gross weight approx.	12 kg
Shipping weight	25,5 kg

### Services (optional)

Article number for conformity assessment 965-201

Article number for DAkkS calibration	963-101
Article number for certificate of conformity (verification)	969-517

#### Pictograms

#### STANDARD



#### **OPTION**

]	DAkkS	
ſ	+3 DAYS	

FACTORY



