KERN 283-602



Precise, mechanical force gauge in robust aluminium housing with Newton readout



Functions

Category	
Brand	Sauter
Product categoriy	Force measuring device
Product group	Spring balance (Newton scale)
Product family	283

Measuring System	
Default unit	N
Tolerance (% of [Max])	0,3%
Measuring range force [Max] (N)	200 N
Readability force [d] (N)	2 N
Directions of force	tension
Overload protection (% of [Max])	1%

Construction	
Dimension housing (W×D×H)	370×32×32 mm
Housing diameter (Ø)	32 mm
Length loaded (I [Max])	510 mm
Length unloaded (I [Min])	370 mm
Dimensions completely mounted (W×D×H)	370×32×32 mm
Material housing	aluminium
Load support (tensile force)	Hook

Peak function	✓
Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	412×40×40 mm
Net weight	0 44 kg

Shipping method	Parcel service
Net weight approx.	0,45 kg
Gross weight approx.	0,55 kg
Shipping weight	0,514 kg

Services (optional)	
Article number for factory calibration	961-1610
Article number for factory calibration (tensile force)	961-1610

Pictograms

STANDARD



OPTION



1