
KERN ABT 320-4NM







Category	
Brand	KERN
Product categoriy	Laboratory balance
Product group	Analytical balance
Product family	ABT

Measuring System	
Conformity assessment possible	✓
Construction type of the scale	Single-range balance
Weighing system	Single-Cell
Weighing capacity [Max]	320 g
Weighing capacity [Max] (ct)	1600 ct
Readability [d]	0,0001 g
Readability carat [d] (ct)	0,001 ct
Resolution	3.200.000
Linearity	± 0,0003 g
Reproducibility	0,0001 g
Tare range	320 g
Default unit	g
Units	g ct
Units (if device is conformity assessed)	g ct
Minimum weight [Min]	0,01 g
USP Minimum weight of sample (k = 2, U = 0.1%)	200 mg
Minimum weight [Min] (ct)	0,1 ct
Adjustment options	Adjusting with external weight Internal calibration (automatic) Adjusting with internal weight (manual)

Automatic adjustment - Standard temperature deviation	0,5 °C
Automatic adjustment - Standard time interval	4 h
Stabilization time	4 s
Warm-up time	8 h
Eccentric loading at 1/3 [Max]	0,0005 g

Approval	
CE mark	✓
Pattern approval for conformity assessment	✓
Accuracy classe	1
Verification scale interval [e]	0,001 g
Verification scale interval [e] (ct)	0,01 ct
Conformity assessment possible ex works	✓


Display	
Display type	LCD
Display digit height	14 mm

Construction	
Dimension housing (W×D×H)	217×356×337 mm
Dimensions rectangular draught shield - inner (W×D×H)	168×172×223 mm
Dimensions rectangular draught shield - outer (W×D×H)	200×240×260 mm
Material display housing	Plastics
Material housing	metal
Material weighing plate	stainless steel
Material draught shield	glass
Dimensions weighing surface (Ø)	80 mm
Levelling feet adjustable	✓

Functions	
Number of keys for operation	6
Capacity display	✓
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Function for averaging under unstable weighing conditions	✓
Standby function	✓
Recipe/summing level	Rez A (Net total)
Sum memory function	✓
Underfloor weighing	Hook (included in delivery)

1

KERN ABT 320-4NM





Interfaces RS-232 standard	
----------------------------	--

Counting	
Smallest piece weight when piece counting - laboratory conditions	1 mg
Smallest piece weight when piece counting - normal conditions	10 mg
Counting reference weight can be entered	/
Reference quantity	10, 20, 50, 100
Counting resolution (laboratory conditions)	320.000

Power	Supply

Input voltage power supply / power [Max]	220 V - 240 V AC, 50 Hz
Input voltage device / power [Max]	12 V DC, 1000 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH

Environmental conditions	
Humity of environment [Max]	80 %
Ambient temperature [Min]	10 °C
Ambient temperature [Max]	30 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	50 °C

1 d
405×580×550 mm
7,7 kg
Parcel service
8 kg
12 kg
25,8 kg

Services (optional)	
Article number for conformity assessment	965-201

Article number for DAkkS 963-101 calibration Article number for certificate of 969-517

conformity (verification)

Pictograms

STANDARD

















OPTION



FACTORY

