

# KERN ABJ 220-4NM



The bestseller in analytical balances, with high-quality single-cell weighing system



Automatic adjustment - Standard time interval	4 h
Stabilization time	3 s
Warm-up time	8 h
Eccentric loading at 1/3 [Max]	0,0005 g
Maximum creep (15 minutes)	1 mg
Maximum creep (30 minutes)	2 mg

Approval	
CE mark	✓

Display	
Display type	LCD
Display screen size	115×32 mm
Display backlight	no
Display digit height	14 mm
Languages of the user interface	Symbol language

Construction	
Dimension housing (W×D×H)	213×333×338 mm
Dimensions rectangular draught shield - inner (W×D×H)	174×162×227 mm
Dimensions rectangular draught shield - outer (W×D×H)	201×220×256 mm
Material display housing	Plastics
Material housing	cast aluminium, plastic
Material weighing plate	stainless steel
Material draught shield	glass
Dimensions weighing surface (Ø)	91 mm
Levelling feet adjustable	✓

Functions	
Number of keys for operation	6
Auto-off interval(s) in mains power mode	0 - 99 min
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Tolerance weighing	✓
Tolerance weighing - type of signal	visual
Standby function	✓
Recipe/summing level	Rez A (Net total)
Sum memory function	✓
Underfloor weighing	None
Interfaces	RS-232 (optional)

Category	
Brand	KERN
Product category	Laboratory balance
Product group	Analytical balance
Product family	ABJ

Measuring System	
Construction type of the scale	Single-range balance
Weighing system	Single-Cell
Weighing capacity [Max]	220 g
Weighing capacity [Max] (ct)	1100 ct
Readability [d]	0,0001 g
Readability carat [d] (ct)	0,001 ct
Resolution	2.200.000
Linearity	± 0,0003 g
Reproducibility	0,0002 g
Default unit	g
Units	g mg ct
Units (if device is conformity assessed)	g mg ct
USP Minimum weight of sample (k = 2, U = 0.1%)	400 mg
Minimum weight [Min] (ct)	0,1 ct
Adjustment options	Internal calibration (automatic) Adjusting with internal weight (manual)
Automatic adjustment - Standard temperature deviation	2 °C

# KERN ABJ 220-4NM



The bestseller in analytical balances, with high-quality single-cell weighing system

## Counting

Smallest piece weight when piece counting - laboratory conditions	1 mg
Smallest piece weight when piece counting - normal conditions	10 mg
Counting reference weight can be entered	✓
Reference quantity	5, 10, 20, 50, 100
Counting resolution (laboratory conditions)	220.000

## Power Supply

Input voltage power supply / power [Max]	110 V - 230 V AC
Input voltage device / power [Max]	12 V DC, 1000 mA
Plug-in power supply type	Power adapter
Supplied power supply	Power supply unit
Plug-in power supply / adapter for countries - included with the delivery	EURO AUS UK US CH
Plug-in power supply / adapter for countries - optional	EURO AUS UK US CH

## Environmental conditions

Humidity of environment [Min]	20 %
Humidity of environment [Max]	85 %
Ambient temperature [Min]	10 °C
Ambient temperature [Max]	30 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	50 °C

## Packing & Shipping

Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	390×560×520 mm
Net weight	6,345 kg
Shipping method	Parcel service
Net weight approx.	7 kg
Gross weight approx.	10 kg
Shipping weight	22,7 kg

## Services (optional)

Article number for DAkkS calibration	963-101
--------------------------------------	---------

Article number for certificate of conformity (verification) 969-517

## Pictograms

### STANDARD



### OPTION

