
KERN ABT 100-5NM







Category	
Brand	KERN
Product categoriy	Laboratory balance
Product group	Analytical balance
Product family	ABT

Measuring System	
Conformity assessment possible	✓
Construction type of the scale	Single-range balance
Weighing system	Single-Cell
Weighing capacity [Max]	101 g
Weighing capacity [Max] (ct)	505 ct
Readability [d]	0,00001 g
Readability carat [d] (ct)	0,0001 ct
Resolution	10.100.000
Linearity	± 0,00015 g
Reproducibility	0,00005 g
Tare range	101 g
Default unit	g
Units	g ct
Units (if device is conformity assessed)	g ct
Minimum weight [Min]	0,001 g
USP Minimum weight of sample (k = 2, U = 0.1%)	100 mg
Minimum weight [Min] (ct)	0,01 ct
Adjustment options	Adjusting with external weight Internal calibration (automatic) Adjusting with internal weight (manual)

Automatic adjustment - Standard temperature deviation	0,5 °C
Automatic adjustment - Standard time interval	4 h
Stabilization time	10 s
Warm-up time	8 h
Eccentric loading at 1/3 [Max]	0,00015 g

Approval	
CE mark	✓
Pattern approval for conformity assessment	✓
Accuracy classe	1
Verification scale interval [e]	0,001 g
Verification scale interval [e] (ct)	0,01 ct
Conformity assessment possible ex works	1


Display		
Display type	LCD	
Display digit height	14 mm	

Construction	
Dimension housing (W×D×H)	217×356×338 mm
Dimensions rectangular draught shield - inner (W×D×H)	168×172×223 mm
Dimensions rectangular draught shield - outer (W×D×H)	200×240×260 mm
Material display housing	Plastics
Material housing	metal
Material weighing plate	stainless steel
Material draught shield	glass
Dimensions weighing surface (Ø)	80 mm
Levelling feet adjustable	✓

Functions	
Number of keys for operation	6
Capacity display	✓
Tare function	manual (multi)
Percentage determination	✓
Counting function	✓
Function for averaging under unstable weighing conditions	✓
Standby function	✓
Recipe/summing level	Rez A (Net total)
Sum memory function	✓
Underfloor weighing	Hook (included in delivery)

1

KERN ABT 100-5NM





Interfaces	RS-232 standard

Odditting		
Smallest piece	weight when piece	

counting - laboratory conditions Smallest piece weight when piece

counting - normal conditions Counting reference weight can be

Reference quantity

Counting resolution (laboratory conditions)

1 mg

10 mg

10, 20, 50, 100

101.000

Power Supply

entered

Input voltage power supply / power [Max]

Input voltage device / power [Max] 12 V DC, 1000 mA Plug-in power supply type

Supplied power supply

Plug-in power supply / adapter for countries - included with the delivery

Plug-in power supply / adapter for countries - optional

110 V - 230 V AC

Power adapter Power supply unit

EURO AUS UK US CH

EURO AUS

UK US СН

Environmental conditions	
Humity of environment [Max]	80 %
Ambient temperature [Min]	10 °C
Ambient temperature [Max]	30 °C
Storage temperature [Min]	-10 °C
Storage temperature [Max]	50 °C

Packing & Shipping	
Readability force [d] (N)	1 d
Dimensions packaging (W×D×H)	433×684×647 mm
Net weight	7,529 kg
Shipping method	Parcel service
Net weight approx.	8 kg
Gross weight approx.	13 kg
Shipping weight	38,3 kg

Services (optional)	
Article number for conformity	965-201
assessment	703-201

Article number for DAkkS 963-101 calibration

Article number for certificate of conformity (verification)

969-517

Pictograms

STANDARD





















OPTION



FACTORY

